



Pass and Seymour
Turnlok® 20A Watertight Connector, NEMA 4X/6P, Yellow
Part No. 27W47



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour Turnlok watertight plugs and connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color-coded sealing bushings provided for large range of cord diameters

For Covering Patents, see www.legrand.us/patents.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Devices resist high-pressure hosedown of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed

Dimensions

Product Width US	1.85 in	Product Depth US	4.03 in
Product Height US	1.85 in		

Technical Information

Phase	Single	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole

Wire Size

14 - 10 AWG

Voltage

125.0 V

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,
66, 67 (Plug & Connector only) Flammability
UL94V0 (boxes & wiring device interiors) Operating
Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed material s
are UV stabilized
