



Pass and Seymour
Trademaster® 15A 125V Tamper-Resistant Duplex Receptacle, White
Part No. 3232TRW



15A/125A Trademaster® Tamper-Resistant Duplex Receptacle

Features & Benefits

Quality Materials, durability, and time-tested design

Rated 15 amperes

Wire Size: #12 - #14 AWG, Solid wire

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Residential, Tamper-Resistant
Application Sector	Residential/Commercial	Standard	UL 498
Type	Outlet		

Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
---------------------	-----	----------	------

Number of Poles	Double Pole	Wire Size	14 - 12 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------
