



Pass and Seymour  
50A 125/250V 14-50R Straight Blade Single Surface Receptacle, 3-Pole, 4-Wire  
Part No. 3854



Straight Blade Power Outlet Surface Receptacle, Range 50A 125/250V

## Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Standard	UL 498

### Dimensions

Product Width US	2.8 in	Product Depth US	2.41 in
Product Height US	5.65 in		

### Technical Information

Connection	Wire Ground	Number of Wires	4
Amperage	50 A	Number of Poles	3-Way
Wire Size	4	Voltage	125.0 V