



Pass and Seymour
30A 125/250V 10-30R Straight Blade Single Flush Receptacle, 3-Pole, 3-Wire
Part No. 3860



Straight Blade Receptacle 30A 125/250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Standard	UL 498		

Dimensions

Product Width US	2.5 in	Product Depth US	1.9 in
Product Height US	3.75 in		

Technical Information

Connection	Non Ground	Number of Wires	3
Amperage	30 A	Number of Poles	3-Way
Wire Size	4	Voltage	125.0 V