



On-Q
Cat 6 Patch Cable, 14 ft, Blue
Part No. AC3614BEV1



This component rated Cat 6 patch cable is constructed with a low profile, snagless boot that protects the tab from catching on other cables in a high density patch panel application. These patch cables are 100% tested an

Features & Benefits

250 MHz patch cable fully supports 10 Gigabit Ethernet speeds

UL verified to support the Cat 6 performance patch cable specification.

Snagless overmold prevents insertion tab from catching on other cables.

Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart.

Specifications

General Info

Product Line	On-Q	UPC Number	804428066842
Country Of Origin	China	Application Sector	Residential
Standard	UL, CSA, FCC, TIA/EIA-568-B2-1 meets or exceeds Cat 6 standards, 94V-0 Flame Retardant, RoHS		