



Turn lights on or off, or even dim them, with just a soft tap of a finger thanks to inventive micro-movement technology. Plus, as a Tru-Universal Dimmer, this dimmer switch self-calibrates to work with virtually any 120V dimmable bulb or fixture (excludes 0-10V). Always adjust to the precise light level you want, without the flicker.

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required.

Perfect for adding precise light level control – all it takes is a soft tap to turn on/off or adjust brightness.

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

Usable in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-------------------|----------------|-------------------------|--|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | Magnesium | Finish | Frosted |
| Country Of Origin | China | Features | Antimicrobial Protection, Indicator Lights |

| | | | |
|------------------------------|---|--------------------|---------------------------|
| Switch Type | sofTap | Number of Switches | 1 |
| Application Sector | Residential | Warranty Type | Limited Lifetime Warranty |
| Type | Dimmer | | |
| Dimensions | | | |
| Product Width US | 1.79 in | Product Depth US | 1.77 in |
| Product Height US | 4.2 in | | |
| Technical Information | | | |
| Electrical Rating | 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent), 120V 8A (EFL) | Number of Gangs | 1 |
| Bulb Compatibility | CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon | Number of Poles | Single Pole 3-Way |
| Indoor/Outdoor | Indoor | Wattage | 700 W |
| Mounting Type | Box | Voltage | 120.0 V |
| Connection Type | Internal Pressure Plates | | |