

Auxiliary Contact Kit, 60As



Features & Benefits

Moisture-Resistant

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
Country Of Origin	Germany	Application Sector	Industrial
Standard	UL, CSA		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Contact Configuration	1 N.O. & 1 N.C.	Contact Rating	10A @ 600VAC
Amperage	60 A	Voltage	600.0 V

Environmental Conditions

Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability:
Flammability: UL94 5VA and VO Classification: UV Resistance: All enclosure materials are UV stable