



On-Q
In Wall TV Power Kit with USB White
Part No. CPU306WV1



Easily hide power and AV cables inside the wall without modifying electrical wiring. This pre-wired kit includes everything needed to extend power for a wall mounted TV while providing the ultimate flexibility with the innovative decorator based power inlet strap and the recessed box with Dual USB Type A receptacle. Kit includes a Dual USB-A Tamper Resistant Outlet to power compatible streaming devices.

Features & Benefits

High-speed Cat 5e termination point for digital data services

Compatible with all TV power plugs, USB type A connections even right angle cords

Hook up a digital TV adapter, cable box, sound bar, or streaming media devices such as Apple TV™ or Roku™

Unique brush strap cable catcher prevents cables from falling behind the wall

Unique decorator based power inlet strap provides flexible project support for ganging other AV connections

Specifications

General Info

Product Line	On-Q	Replaced by Part Number	
Color	White	Finish	Matte
UPC Number	804428434658	Country Of Origin	China
Included	Cutting template, Mounting Hardware	Outlet Type	Indoor, Residential, Tamper-Resistant
Application Sector	Residential	Warranty Type	1 Year from Day of Sale
Type	Tamper-Resistant		

Listing Agencies / 3rd Party Agencies

ETL Listed Yes

Technical Information

Connection	(2) USB Type A, (1) Cable Access, (2) Outlets	Amperage	15 A
Input Voltage	125 V	Indoor/Outdoor	Indoor
Mounting Type	Wall	Operating Temperature	32°-122°F
