



**On-Q**  
**42-inch Plastic Enclosure with Trim Ring and Hinged Door**  
Part No. ENP4250NA



Our 42-inch plastic enclosure with trim ring and hinged door is perfect for custom homes that require several different modules. It's constructed with a robust, wireless transparent ABS plastic material and is a light, low-profile designed to integrate wireless devices into traditional structured wiring installations. The universal mounting grid is compatible with a large variety of third party devices from routers to streaming devices like Apple TV and Roku to 8 port giga switch to power strips and more. Additionally, it is large enough to future proof for larger installations. The enclosure mounts easily for both surface and recessed applications and the hinged door is equipped with extra venting along the vertical plane for superior heat dissipation.

## Features & Benefits

Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference

Extruded cover adds 1.2" of depth for cable headroom and 3rd party device compatibility

Universal mounting grid maximizes compatibility with 3rd party products without additional brackets.

Extra venting along the vertical plane of the door allows for superior heat dissipation

Staggered mounting tabs allow multiple enclosures to mount in adjacent stud bays

Cover includes metal hinge that attaches to left or right side of enclosure in seconds.

Lockable with provided screws.

Tapered design allows enclosures and covers to stack for efficient transportation and warehousing

UL listed.

## Specifications

### General Info

|                   |               |                         |              |
|-------------------|---------------|-------------------------|--------------|
| Product Line      | On-Q          | Replaced by Part Number |              |
| Color             | White         | UPC Number              | 804428433972 |
| Country Of Origin | United States | Package Quantity        | 1            |
| Type              | Enclosure     |                         |              |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 17.48 in | Product Depth US | 4.17 in |
| Product Height US | 42.8 in  |                  |         |

---

## Technical Information

---

Enclosure Type

Traditional

---