



Wattstopper High/Low PIR Fixture Mount Sensor Line Voltage Part No. FSP-211-U



The FSP-211 mounts in an outdoor lighting fixture and provides multi-level control based on motion and/or daylight contribution. It controls 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, is rated for wet and cold locations. All control parameters are adjustable via a wireless configuration tool capable of storing and transmitting sensor profiles.

Features & Benefits

Fully adjustable high and low dimmed light levels; optional dusk to dawn control	Designed for LED fixtures; rated for extreme temperatures and up to 200,000 on/off cycles
Hold off setpoint with automatic calibration option for convenience and added energy savings	Adjustable via handheld wireless configuration tool
IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'	Adjustable time delay and cut off delay

Specifications

General Info

Product Line	Wattstopper	UPC Number	754182934522
Country Of Origin	United States		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Sensor Type	Daylight, Occupancy
-------------	---------------------