



Pass and Seymour  
20A 250V NEMA L620 Single Receptacle, 3-Wire, Black  
Part No. L620R



Turnlok® Receptacle Single 3-Wire 20A 250V

## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Commercial, Indoor
Application Sector	Industrial	Standard	UL 498
Type	Outlet		

### Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

## Technical Information

---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Wire Size	4 AWG	Indoor/Outdoor	Indoor
-----------	-------	----------------	--------

---

Voltage	125.0 V
---------	---------

---