

Replacement cover for use with Non-Fusible Safety Switch PS30SS.

# Product Image Coming

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Industrial
Standard	UL, CSA		

### Dimensions

Product Width US	4.9 in	Product Depth US	6.52 in
Product Height US	8.4 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Contact Configuration	(Optional) 1 N.O. & 1 N.C.	Contact Rating	(Optional) 10A @ 600VAC
Amperage	30 A	Voltage	600.0 V

---

Environmental Conditions

Moisture Resistance: Per UL50, Section 35, NEMA  
Enclosure Type 4X (watertight, hosedown), Type  
12K (dusttight, falling dirt), and IP67 suitability:  
Flammability: UL94 5VA and V0 Classification: UV  
Resistance: All enclosure materials are UV stable

---