



Straight Blade Connector 2-Pole 3-Wire 20A 125A

## Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Nylon housing provides impact and chemical resistance. Rugged two-piece cord grip provides more uniform cord retention. Internal dust shield keeps terminals free of contaminants.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Standard	UL 498
Type	Straight Blade		

### Dimensions

Product Width US	1.516 in	Product Length US	2.638 in
------------------	----------	-------------------	----------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

---

Connection	Wire Grounding	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	4	Voltage	125.0 V

---