



radiant Collection
RADIANT LED DIMMER 250W SP/3W TRI COLOR
Part No. RHL373PTC



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with LED 2-wire bulbs and fixtures compliant with the SSL 7A standard for energy efficiency. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Designed to save energy, this dimmer is for use with LED bulbs and fixtures also designed to the SSL 7A standard for efficiency. For use in both single-pole and 3-way applications.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

No derating* required for 2-gang applications. *Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|--------------------|----------------------------|-------------------------|---------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | Ivory, Light Almond, White | Finish | Matte |
| Country Of Origin | China | Features | Locator Light |
| Switch Type | Paddle, Slider | Number of Switches | 1 |
| Application Sector | Residential | Warranty Type | Limited Lifetime Warranty |
| Type | Dimmer | | |

Dimensions

| | | | |
|------------------|---------|------------------|--------|
| Product Width US | 1.29 in | Product Depth US | 1.0 in |
|------------------|---------|------------------|--------|

| | |
|-------------------|---------|
| Product Height US | 3.18 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|-----------------|---|----------|-------|
| Number of Gangs | 1 | Amperage | 2.1 A |
|-----------------|---|----------|-------|

| | | | |
|--------------------|---------------------------------|-----------------|--------------------|
| Bulb Compatibility | CFL, Halogen, Incandescent, LED | Number of Poles | 3-Way, Single Pole |
|--------------------|---------------------------------|-----------------|--------------------|

| | | | |
|---------|-------|---------------|-----|
| Wattage | 300 W | Mounting Type | Box |
|---------|-------|---------------|-----|

| | |
|---------|---------|
| Voltage | 120.0 V |
|---------|---------|
