




radiant Collection  
radiant® 4-Button Digital Timer, White  
Part No. RT2W



Installs easily in place of a standard light or fan switch, or older spring-wound timer and includes manual on/off through the paddle switch for added convenience. A locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Works with a variety of light bulbs or fixtures, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Automates control of lights for energy and cost savings. Also includes manual on/off through the paddle switch for added convenience.

Lets you select a desired preset shut-off time, including 60, 40, 20 and 10 minutes.

Installs easily in place of a standard light or fan switch, or older spring-wound timer.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	White	Country Of Origin	China
Features	Timer	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential/Commercial
Standard	cULus	Warranty Type	5-Year
Type	Switch		

### Dimensions

---

Product Width US	1.69 in	Product Depth US	1.88 in
------------------	---------	------------------	---------

---

Product Height US	3.281 in
-------------------	----------

---

### Technical Information

---

Connection	Back & Side Wired	Coil Voltage	120 V
------------	-------------------	--------------	-------

---

Contact Rating	600Watts	Number of Gangs	1
----------------	----------	-----------------	---

---

Number of Buttons	4	Amperage	15 A
-------------------	---	----------	------

---

Action	Single Pole	Number of Poles	Single Pole
--------	-------------	-----------------	-------------

---

Indoor/Outdoor	Indoor	Timing Range	10-60 minutes
----------------	--------	--------------	---------------

---

Wattage	600 W	Mounting Type	Box
---------	-------	---------------	-----

---

Voltage	120.0 V
---------	---------

---