



Wiremold
Plugmold Hard-Wired Multi-Outlet Strip 3 foot long with receptacles 6 inches on center, Ivory
Part No. V20GB306

The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.



Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

Specifications

General Info

| | | | |
|-----------------------|---|--------------------|------------------------|
| Product Line | Wiremold | Color | Ivory |
| UPC Number | 786776093162 | Country Of Origin | United States |
| Number of Receptacles | 6 | Application Sector | Residential/Commercial |
| Standard | cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7 | Type | Plugmold |

Dimensions

| | | | |
|-------------------|------------|-------------------|---------|
| Product Width US | 36.0 in | Product Weight US | 1.79 lb |
| Product Volume US | 39.6 cu in | Product Depth US | 0.88 in |

Product Height US 1.25 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber E15191 cULus Listed Yes

Buy American Act Compliance

NAFTA Yes

Additional Information

RoHS Conformant Yes Product Environmental Profile Yes

Technical Information

Frequency Rating 60 Hz Amperage 15 A

Enclosure Type Steel Voltage 125.0 V

Environmental Conditions Dry interior locations
