



Pass and Seymour
50A 250V 6-50R Straight Blade Single Surface Receptacle, 2-Pole, 3-Wire
Part No. 3852



Straight Blade Receptacle 2-Pole Wire 50A 250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Standard	UL 498

Dimensions

Product Width US	2.8 in	Product Depth US	2.41 in
Product Height US	5.65 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection	Wire Ground	Number of Wires	3
Amperage	50 A	Number of Poles	Double Pole

Wire Size

4

Voltage

250.0 V
