



**Pass and Seymour**  
**Double Pole, Single Phase AC Manual Motor Controller**  
Part No. 7812PMD



Double Pole, Single Phase AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.

## Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed

### Dimensions

Product Width US	2.825 in	Product Depth US	2.8 in
Product Height US	3.91 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Amperage	30 A
Enclosure Type	NEMA 1	Voltage	600.0 V
Environmental Conditions	UL94 V2		

---