



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

Features & Benefits

- Height adjustable: For support of cable pathways with varying heights . Base includes: two (2) 1/2' Electrozinc threaded rod risers and FAS Profile or channel.
- Install on any roofing material . Supports are available in three finishes.
- Standard series maximum load: 150 lbs. Widebody design: has maximum load of 500 lbs. Provides 5 times the surface area to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

Specifications

General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388019515	Country Of Origin	United States

Buy American Act Compliance

BAA	Yes
-----	-----
