



On-Q  
Cat 6 Patch Cable, 25 ft, Blue  
Part No. AC3625BEV1



This component rated Cat 6 patch cable is constructed with a Low profile snagless boot that protects the tab from catching on other cables in highdensity patch panel application. These patch cables are 100% tested and exceed the patch cable standards

## Features & Benefits

250 MHz patch cable fully supports 10 Gigabit Ethernet speeds

UL verified to support the Cat 6 performance patch cable specification.

Snagless overmold prevents insertion tab from catching on other cables.

Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart.:

## Specifications

### General Info

Product Line	On-Q	UPC Number	804428066859
Country Of Origin	China	Application Sector	Residential
Standard	UL, CSA, FCC, TIA/EIA-568-B2-1 meets or exceeds Cat 6 standards, 94V-0 Flame Retardant, RoHS		