




adorne Collection  
adorne® Touch Tru-Universal Dimmer, Magnesium, with Microban®  
Part No. ADTH703TUM4



This dimmer switch from the adorne Collection features a translucent, glass-like face and operates with the simple touch of a finger on the center circle to turn lights on/off, or by using the + or - on the side to dim. In multi-gang installations, we recommend using the Touch-control modern light switches and dimmers together for consistency of control and aesthetic. A Tru-Universal Dimmer, this device self-calibrates to work with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

This dimmer\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

Offers installation flexibility, working in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

Constant memory feature returns lights to their previous level when turning back on or after a power outage.

Usable in both single-pole and 3-way applications.

## Specifications

### General Info

Product Line

Pass & Seymour

Replaced by Part Number

Color	Magnesium	Country Of Origin	China
Features	Antimicrobial Protection, Indicator Lights	Switch Type	Touch
Number of Switches	1	Warranty Type	Limited Lifetime Warranty
<b>Dimensions</b>			
Product Width US	1.77 in	Product Depth US	1.29 in
Product Height US	2.48 in		
<b>Technical Information</b>			
Electrical Rating	120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL)	Number of Gangs	1
Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon	Number of Poles	3-Way, Single Pole
Wattage	700 W	Mounting Type	Box
Voltage	120.0 V	Connection Type	Internal Pressure Plates