




adorne Collection  
adorne® Bronze One-Gang Screwless Wall Plate with Microban®  
Part No. AWP1G2BR6



A rich complement to stately shades and earth tone, with a hint of warmth. Made exclusively for use with designer switches and outlets from the adorne® Collection. This wall plate\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product. \* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label. No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology.

Made to exclusively fit the designer switches, dimmers and outlets from the adorne® Collection, snapping into place with ease.

Coordinate with other designer switches and outlets throughout your home for a cohesive, contemporary look.

Includes one Wall Plate and one Steel Frame for mounting the wall plate.

Other Wall Plates from the adorne® Collection are available in extensive range of on-trend colors, materials and cast metals.

A perfect finishing touch for any space, adding a sleek and contemporary aesthetic through its screwless design and low-profile.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Bronze	Country Of Origin	Mexico
Construction	Screwless Design Snaps into Frame	Wall Plate Type	Dimmer/Switch, Outlet
Application Sector	Residential/Commercial	Standard	cULus UL514, cETLus
Warranty Type	Limited Lifetime Warranty		

### Dimensions

Product Width US	3.45 in	Product Depth US	0.35 in
Product Height US	5.13 in		

---

## Technical Information

---

Cutout	Square	Thickness	0.07 in
Number of Gangs	1	Mounting Type	Screwless
Orientation	Horizontal	Connection Type	Screwless

---