

Auxiliary Contact Kit, 30A



## Features & Benefits

Moisture-Resistant

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Blue
Country Of Origin	Germany	Application Sector	Industrial
Standard	UL, CSA		

### Dimensions

Product Width US	3.19 in	Product Depth US	1.38 in
Product Height US	4.94 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

### Technical Information

Contact Configuration	1 N.O. & 1 N.C.	Contact Rating	10A @ 600VAC
Amperage	30 A	Voltage	600.0 V

---

Environmental Conditions      Moisture Resistance: Per UL50, Section 35, NEMA  
Enclosure Type 4X (watertight, hosedown), Type  
12K (dusttight, falling dirt), and IP67 suitability:  
Flammability: UL94 5VA and V0 Classification: UV  
Resistance: All enclosure materials are UV stable

---