



On-Q
14-inch Enclosure, No Cover
Part No. EN1480



This 14" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

Features & Benefits

Includes five openings on the top of the enclosure with knockouts

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023050	Country Of Origin	United States
Package Quantity	1	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in		

Listing Agencies / 3rd Party Agencies

CSA Listed

Yes

cULus Listed

Yes

Additional Information

RoHS Conformant

Yes

Technical Information

Thickness

0.1 in

Enclosure Type

Traditional

Cable Entry

(6) rear knockouts,(2) rectangular knockouts for 1-gang electrical box,(3) top knockouts

Frame

Cold Rolled Steel
