



**On-Q**  
**28-inch Enclosure with Screw-On Cover**  
Part No. EN2800



This 28" enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a sc

## Features & Benefits

28-in Enclosure with Screw-On Cover

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Literature pouch included for dealer information

Includes self-adhesive cable identification table

Cover included

Made in the USA

## Specifications

### General Info

|                  |  |                    |               |
|------------------|--|--------------------|---------------|
| Product Line     | On-Q   | Color              | White         |
| UPC Number       | 804428023111                                 | Country Of Origin  | United States |
| Package Quantity | 1  | Application Sector | Residential   |
| Standard         | UL (UL985, UL1023, UL1863), cULus, CSA, RoHS | Type               | Enclosure     |

### Dimensions

|                   |          |                  |        |
|-------------------|----------|------------------|--------|
| Product Width US  | 14.25 in | Product Depth US | 3.6 in |
| Product Height US | 28.0 in  |                  |        |

---

## Listing Agencies / 3rd Party Agencies

---

|            |     |              |     |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

---

## Additional Information

---

|                 |     |                               |     |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|

---

## Technical Information

---

|             |  |                |                   |
|-------------|--|----------------|-------------------|
| Thickness   | 0.1 in   | Enclosure Type | Traditional       |
| Cable Entry | (2) rectangular knockouts for 1-gang electrical box,(6) rear knockouts,(3) top knockouts | Frame          | Cold Rolled Steel |

---