



**On-Q**  
**42-inch Enclosure with Hinged Door**  
Part No. EN4250



Perfect for larger installations, this 42" enclosure features universal On-Q style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more s

## Features & Benefits

42-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Literature pouch included for dealer information
Includes self-adhesive cable identification table	Cover included
Made in the USA	

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428023180	Country Of Origin	United States
Package Quantity	1	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	42.0 in		

### Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

---

### Additional Information

---

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

---

### Technical Information

---

Thickness	0.1 in	Enclosure Type	Traditional
Cable Entry	(6) rear knockouts,(3) top knockouts,(2) rectangular knockouts for 1-gang electrical box	Frame	Cold Rolled Steel

---