



Turnlok® Single Receptacle 4-Wire 20A 125/250V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

| | | | |
|-----------------------|----------------|-------------------|--------------------|
| Product Line | Pass & Seymour | Color | Black |
| Finish | Matte | Country Of Origin | Mexico |
| Number of Receptacles | 1 | Outlet Type | Commercial, Indoor |
| Application Sector | Industrial | Standard | UL 498 |
| Type | Outlet | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.61 in | Product Depth US | 1.19 in |
| Product Height US | 2.29 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------|----------------|--------|
| Wire Size | 4 AWG | Indoor/Outdoor | Indoor |
|-----------|-------|----------------|--------|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
