

Turnlok® Single Receptacle 4-Wire 30A 125/250V



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Black      |
| Country Of Origin | Mexico         | Application Sector | Industrial |
| Standard          | UL 498         |                    |            |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.61 in | Product Depth US | 1.28 in |
| Product Height US | 2.42 in |                  |         |

### Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

### Additional Information

---

|                 |     |                               |     |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|

---

### Technical Information

---

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 30 A |
|-----------------|---|----------|------|

---

|                 |             |           |       |
|-----------------|-------------|-----------|-------|
| Number of Poles | Double Pole | Wire Size | 4 AWG |
|-----------------|-------------|-----------|-------|

---

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|

---