



Ortronics

Infinium Ultra M4 Cassette - 24 Fiber - LC Duplex to MPOM - OM4 - Universal Polarity

Part No. LM4-LC24H-3C3UN

Infinium M4 Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution can enable industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

LC adapter with Internal shutter: Provides eye safety by attenuating laser light when the mated connector is removed - 100% automatic shutter mechanism requiring no operator handling of the shutter door - Compatible with standard LC connectors - It keeps adapter's interior clean from dust - You can see the visible light through the adapter

Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber

Benefits of Base 8 Connectivity: Optimized for 8-fiber transceivers and transmission technologies, 100% fiber utilization for 8-fiber transceiver systems, Cable harnesses match common port counts on network devices, Flexibility for easy migration to 40G/100G/400G networks

Specifications

General Info

Product Line	Ortronics	UPC Number	662875031161
Country Of Origin	United States	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

Dimensions

Product Width US	4.24 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Performance Level/Tier	Infinium Core
------------------------	---------------