



Pass and Seymour

LS Series CFL/LED/Incandescent Single Pole/3-Way Slide Dimmer with Single Pole/3-Way, 3-Speed De-Hummer Fan Control, Preset, White
Part No. LSCLDC163PWCCV4



The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)

Single pole/3-way versions

Unique integrated single pole/3-way dimmer with fan speed control

Ratings: 150W LED & CFL: 300W Incandescent: 1.6A (Fan Control): 120VAC 60Hz

Specifications

General Info

| | | | |
|-------------------|---------------------------|--------------------|-----------------------------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Features | Combination, Fan Control, Locator Light |
| Switch Type | Push, Slider | Number of Switches | 2 |
| Warranty Type | Limited Lifetime Warranty | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 2.5 in | Product Depth US | 1.28 in |
| Product Height US | 4.19 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|-----------------|--------------------|--------------------|------------------------|
| Amperage | 1.6 A | Bulb Compatibility | CFL, Incandescent, LED |
| Number of Poles | 3-Way, Single Pole | Wattage | 300 W |
| Voltage | 120.0 V | | |