



Ortronics  
Infinium M4 Cassette 12 Fiber, LC, OM4, Type B, Near End  
Part No. M4LCD12-50EC3A1



Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.

## Features & Benefits

Method B connectivity: Has flipped polarity and uses key-up to key-up adapters

Fiber port labeling: Provides easier administration

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875001218
Country Of Origin	China	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

### Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

### Additional Information

RoHS Conformant	Yes
-----------------	-----