



Pass and Seymour Non-Fusible Mechanical Interlock

Part No. PS560MIR9W



4-Pole, 5-Wire, Non-Fusible Mechanical Interlock Receptacle. 60A, 3Y, 120/208V

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Industrial
Standard	UL Listed		

Dimensions

Product Width US	6.88 in	Product Depth US	9.0 in
Product Height US	9.0 in		

Technical Information

Phase	Three	Number of Wires	5
Amperage	60 A	Number of Poles	4-Way
Voltage	120.0 V		