



PlugTail® Hospital-Grade 20A Self-Test GFCI Receptacle. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Plated steel wrap strap design for maximum durability and corrosion resistance.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Commercial, GFCI, Indoor, Self-Test	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
------------------	-----	------------------	-------

Trip Range	5±1 mA	Connection	Built-in Connector
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		
