



radiant Collection
radiant® Incandescent 700W Dimmer, White
Part No. RH703PW



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with incandescent bulbs and fixtures. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

For use with incandescent bulbs and fixtures on typical residential (and light commercial) wiring. Usable in both single-pole and 3-way applications. Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Screw pressure plate back wire allows easier installation and fit into the wall box

Eliminates the need to derate LED bulbs when in multi-gang situations

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	White	Finish	Matte
Country Of Origin	China	Switch Type	Paddle, Slider
Number of Switches	1	Application Sector	Residential
Standard	cULus, CSA Listed, UL 1472	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Preset	Preset, Single-Pole and 3-Way	Compatibility	Incandescent Load
Frequency Rating	60 Hz	Connection	Screw Terminals
Number of Gangs	1	Amperage	15 A
Bulb Compatibility	Incandescent	Number of Poles	3-Way, Single Pole
Indoor/Outdoor	Indoor	Wattage	700 W
Mounting Type	Box	Supply Voltage	120 VAC
Voltage	120.0 V	Load	Incandescent
Environmental Conditions	95% (relative humidity, non-condensing)		
