

Long Range  Sensor, Passive Infrared, 24volt DC, White



Features & Benefits

Detection Signature Analysis provides high immunity to RFI and EMI.

2 coverage patterns to choose from.

Wall mount or ceiling mount.

Adjustable sensitivity settings.

Digital time delay from 15 seconds to 30 minutes.

Dual-element, temperature-compensated pyroelectric sensor.

LED occupancy detection indicator.

Compatible with 120VAC or 277VAC, 60 Hz lighting systems.

Class 2 low-voltage device.

Positive detection indicator.

cULus listed.

5-year warranty.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Commercial	Standard	UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Target Size	1050 sq ft	Operating Cycles	100000
-------------	------------	------------------	--------

Sensor Type	Occupancy	Body	Thermoplastic
Sensitivity	50/60 Hz	Load	120/230/277vac
