



The Cat 6 RJ45 Keystone Coupler couples two high-speed network cables. The female to female coupler meets the EIA/TIA 568A Category 6 specifications.

Features & Benefits

RJ45 Cat 6 Coupler Keystone Insert	Supports up to 10 gigabit Ethernet connection
No tools required	Exceeds Category 6 component standard: Ensures standards compliance

Specifications

General Info

Product Line	On-Q	Color	White
Finish	Matte	UPC Number	804428065968
Country Of Origin	Taiwan, Province Of China	Package Quantity	1
Application Sector	Residential	Standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0
Type	Coupler		

Technical Information

Category Performance Rating	Cat 6	Termination Style	Coupler
Gauge	22 to 24 AWG	Cable Type	Cat 6
Amperage	1.5 A	Operating Temperature	14°-140°F

Environmental Conditions

0 to 93% (relative humidity, non-condensing)
