



Pass and Seymour  
Weatherproof Two Gang Box, Gray  
Part No. WPB382



Weatherproof 2 Gang Box, 7 hole 3/4, 30.5 Cu.In., Gray (2 Holes Each End, 1 Hole Each Side, 1 Hole in Back)

## Features & Benefits

Wide range of sizes, depths, and gangs.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

2 closure plugs and mounting lugs furnished with all boxes.

UL Listed for wet and/or damp locations with appropriate cover.

Designed for both interior and exterior applications.

Will accept standard 4 screw mounting covers and single gang weatherproof covers.

Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.

Heavy die-cast aluminum.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	India	Application Sector	Residential/Commercial
Standard	UL Listed	Type	Weatherproof

### Dimensions

Product Width US	4.5 in	Product Depth US	2.24 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

---

## Technical Information

---

Number of Outlets            2

---