

#### Pass and Seymour 15A Double Pole, Double Throw Switch, Brown Part No. 1222

Double-Pole, Double-Throw Switch, 15A, 120/277V.



# Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.	Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
Fiber terminal insulation barriers standard.	Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
Bodies, covers, and toggles molded of durable nylon.	Single Pole-Double Throw and Double Pole-Double Throw.
Locking Switches supplied with one 1498-NT key.	Normally open.
For covering patents, see https://www.legrand.us/patents.	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates.

# Specifications

General Info					
Product Line	Pass & Seymour	Color	Brown		
Country Of Origin	Mexico	Standard	UL Listed		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17949		

#### Technical Information

Amperage	15 A	Number of Poles	Double Pole
Wattage	2 W	Voltage	120/277 V