

Pass and Seymour Locking 20A Single Pole, Double Throw Switch

Part No. 1225L



Manual Controller Single-Pole, Double-Throw Switch, 20A, 120/277V, Locking.

Features & Benefits

Oversize silver alloy contacts for

long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw only.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see https://www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Standard	UL Listed

Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes		
CSA File Number	17949				
Technical Information					
Amperage	20 A	Wattage	1 W		
Voltage	120.0 V				