



Pass and Seymour
Portable 6-Foot In-Line 15A Self-Test GFCI with Straight Blade Plug and Connector, Manual Reset
Part No. 1597PC6M



The perfect option for safely powering portable equipment, outdoors or in, when a GFCI-protected outlet is not accessible. Use this 6-Foot In-Line Portable GFCI (Manual Reset) when plugging in drills, saws, leaf blowers, pressure washers, power painters, etc.

Ground-Fault Circuit Interrupters (GFCI) help prevent electrical shock caused by ground faults. GFCI protection is required by code in bathrooms, kitchens, garages, outdoor areas, and for any other outlets found within six feet of a sink or water source.

Features & Benefits

Protects against electrical shock caused by ground-fault occurrences.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected. Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged.

Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced.

Requires portable GFCI to be manually set for use by pressing reset button upon plug in and after loss of primary power.

Specifications

General Info

| | | | |
|---------------|-------------------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Finish | Matte | Country Of Origin | China |
| Outlet Type | GFCI | Application Sector | Residential/Commercial |
| Warranty Type | 1-Year Limited Warranty | Type | Straight Blade |

Dimensions

| | | | |
|------------------|---------|-------------------|----------|
| Product Width US | 2.0 in | Product Weight US | 1.3 lb |
| Product Depth US | 1.75 in | Product Length US | 75.75 in |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-----|--------------|-----|
| cULus ListingNumber | 943 | cULus Listed | Yes |
|---------------------|-----|--------------|-----|

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

| | | | |
|-------------------------|--------------|----------------|---------|
| Is Tamper-Resistant | No | Amperage | 15 A |
| Is Weather Resistant | No | Indoor/Outdoor | Outdoor |
| NEMA Configuration Code | 5-15P, 5-15R | Voltage | 125.0 V |
