



Perfect for providing dedicated power and reliable ground-fault protection, the simplex 15A GFCI features a single, tamper-resistant outlet and self-tests automatically every three seconds for electrical safety you can trust. Meeting the National Electrical Code requirements for ground fault protection in the home, GFCI wall outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. Maximize safety, in style, with GFCI plug protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device
- Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected
- Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisible-shutters" for an invisible effect.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced
- Includes green LED illuminated power indication to confirm the receptacle is energized
- Replaces a traditional outlet easily, in as little as 10 minutes
- More color options available to fit any style, including finishes to match current hardware and lighting trends

## Specifications

### General Info

|                    |                         |                         |  |
|--------------------|-------------------------|-------------------------|--|
| Product Line       | Pass & Seymour          | Replaced by Part Number |  |
| Color              | Gray                    | Finish                  | Matte  |
| Country Of Origin  | China                   | Outlet Type             | GFCI, Indoor, Residential, Self-Test, Tamper-Resistant |
| Application Sector | Residential/Commercial  | Standard                | RoHS, cULus  |
| Warranty Type      | 1-Year Limited Warranty | Type                    | GFCI, Tamper-Resistant                                 |

### Dimensions

---

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.73 in | Product Depth US | 1.03 in |
|------------------|---------|------------------|---------|

---

|                   |        |
|-------------------|--------|
| Product Height US | 4.2 in |
|-------------------|--------|

---

#### Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

#### Additional Information

---

|                 |     |   |     |
|-----------------|-----|---|-----|
| RoHS Conformant | Yes | Product Has Potential to Contribute to LEED | Yes |
|-----------------|-----|---|-----|

---

#### Technical Information

---

|                     |     |          |      |
|---------------------|-----|----------|------|
| Is Tamper-Resistant | Yes | Amperage | 15 A |
|---------------------|-----|----------|------|

---

|                      |    |                |        |
|----------------------|----|----------------|--------|
| Is Weather Resistant | No | Indoor/Outdoor | Indoor |
|----------------------|----|----------------|--------|

---

|         |        |                         |       |
|---------|--------|-------------------------|-------|
| Wattage | 1875 W | NEMA Configuration Code | 5-15R |
|---------|--------|-------------------------|-------|

---

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|

---