

radiant Collection radiant® Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, USB Type A/A, Dark Bronze C4 Part No. 1597TRUSBAADBC4



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for Provides reliable ground fault protection with a trip indicator light and reset button on the outlet easier charging, anywhere for easy, accessible troubleshooting Includes traditional power outlets and two USB Type-A ports for Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. convenient charging. Shares 2.0A charging capacity between both Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced ports Equipped with proven SafeLockTM feature which disconnects power Protect children using a patented ""invisi-shutter"" system to prevent the insertion of foreign to the outlet if any critical components are damaged for added objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant protection requirements Installs quickly thanks to a redesigned side wire cavity for easier Can provide ground fault protection to downstream outlets through feed-thru wiring access Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from

Specifications

the radiant® Collection.

General Info

Product Line	Pass & Seymour	Replaced by Part Number			
Color	Dark Bronze	Finish	Matte		
Country Of Origin	China	Number of Receptacles	2		
Construction	Polycarbonate	Features	USB-A Charging		
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant, USB-Charging	Application Sector	Residential/Commercial		
Warranty Type	1-Year Limited Warranty	Туре	Outlet		
Dimensions					
Product Width US	1.73 in	Product Depth US	1.03 in		
Product Height US	4.2 in				
Technical Information					
ls Tamper-Resistant	Yes	USB Amperage	2.1 A		
Number of USBs	2	Number of Gangs	1		

Amperage	15 A	Number of Poles	Double Pole
Is Weather Resistant	No	Indoor/Outdoor	Indoor
Wattage	1875 W	Mounting Type	Box
Voltage	125.0 V		