

radiant Collection

radiant® Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, USB Type A/A, Light Almond





Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for Provides reliable ground fault protection with a trip indicator light and reset button on the easier charging, anywhere outlet for easy, accessible troubleshooting

Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports

Equipped with proven SafeLockTM feature which disconnects added protection

Installs quickly thanks to a redesigned side wire cavity for easier access

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Protect children using a patented ""invisi-shutter"" system to prevent the insertion of power to the outlet if any critical components are damaged for foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Can provide ground fault protection to downstream outlets through feed-thru wiring

Specifications

General Info				
Product Line	Pass & Seymour	Replaced by Part Number		
Color	Light Almond	Finish	Matte	
Country Of Origin	China	Number of Receptacles	2	
Construction	Polycarbonate	Features	USB-A Charging	
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper- Resistant, USB-Charging	Application Sector	Residential/Commercial	
Warranty Type	1-Year Limited Warranty	Туре	Outlet	
Dimensions				
Product Width US	1.73 in	Product Depth US	1.03 in	
Product Height US	4.2 in			

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes		
Additional Information					
RoHS Conformant	Yes				
Technical Information					
Is Tamper-Resistant	Yes	USB Amperage	2.1 A		
Number of USBs	2	Number of Gangs	1		
Amperage	15 A	Number of Poles	Double Pole		
Is Weather Resistant	No	Indoor/Outdoor	Indoor		
Wattage	1875 W	Mounting Type	Вох		
Voltage	125.0 V				