

radiant Collection radiant® Tamper-Resistant Weather-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, NAFTA Compliant, Ivory Part No. 1597TRWRNAI



Adding weather resistance to ground fault protection, this outlet was designed for use on patios, pool areas, and other outdoor living spaces. Like all GFCI outlets from the radiant® Collection, it self-tests automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences, and makes it easier to recognize and fix trips right where they happen – no more running to the breaker box. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements

More color options available to fit any style, including finishes to match current hardware and lighting trends $\,$

NAFTA-Compliant devices are ideal for use on projects subject to the provisions of the Buy America $\operatorname{\mathsf{Act}}$

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

| General Info | | | | |
|---------------------------------------|-------------------------|-------------------------|---|--|
| Product Line | Pass & Seymour | Replaced by Part Number | | |
| Color | lvory | Country Of Origin | Mexico | |
| Number of Receptacles | 2 | Outlet Type | GFCI, Indoor, Self-Test, Tamper-Resistant | |
| Application Sector | Residential/Commercial | Standard | cULus, UL Listed, FSUL | |
| Warranty Type | 1-Year Limited Warranty | | | |
| Dimensions | | | | |
| Product Width US | 1.73 in | Product Depth US | 1.03 in | |
| Product Height US | 4.2 in | | | |
| Listing Agencies / 3rd Party Agencies | | | | |
| cULus Listed | Yes | | | |
| Additional Information | | | | |
| Product Environmental Profile | Yes | | | |

| Technical Information | | | | |
|--------------------------|------------------------|------------------|--------------------|--|
| Interrupt Rating | 4 A | Frequency Rating | 60 Hz | |
| Trip Range | 5±1 mA | Connection | Back and side wire | |
| Number of Gangs | 1 | Amperage | 15 A | |
| Mounting Type | Вох | Voltage | 125.0 V | |
| Environmental Conditions | 95% Humidity, UL 94 V2 | | | |