

radiant Collection

radiant® Tamper-Resistant Weather-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, USB Type A/C Outlets, Black Part No. 1597TRWRUSBACBK



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required. Also including tamper and weather resistance, this model was designed for use on decks, patios, pool areas, and other outdoor spaces. Easily see and reset electrical trips right where they happen, while gaining two USB connections for keeping phones or tablets charged, no bulky adapter necessary. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Includes traditional power outlets, as well as one USB Type-A and one USB Type-C port for convenient charging. Shares 2.0A charging capacity between both ports

if any critical components are damaged for added protection

Protect children using a patented ""invisi-shutter"" system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Provides reliable ground fault protection for use in outdoor spaces, including patios, decks and pool areas. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Equipped with proven SafeLock™ feature which disconnects power to the outlet Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements

> Installs quickly thanks to a redesigned side wire cavity for easier access. Can provide ground fault protection to downstream outlets through feed-thru wiring

Specifications

General Info				
Product Line	Pass & Seymour	Replaced by Part Number		
Color	Black	Finish	Matte	
Country Of Origin	China	Number of Receptacles	2	
Features	USB-A Charging, USB-C Charging	Outlet Type	GFCI, Outdoor, Residential, Self-Test, Tamper- Resistant, USB-Charging	
Application Sector	Residential/Commercial	Warranty Type	1-Year Limited Warranty	
Туре	Duplex, GFCI, Tamper-Resistant, USB, Weather-Resistant			
Dimensions				
Product Width US	1.73 in	Product Depth US	1.03 in	
Product Height US	4.2 in			
Listing Agencies / 3rd Party Agencies				
CSA Listed	Yes	cULus ListingNumber	E140596	
cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 42	
Additional Information				

RoHS Conformant

Technical Information				
Is Tamper-Resistant	Yes	USB Amperage	2.1 A	
Number of USBs	2	Number of Gangs	1	
Amperage	15 A	Is Weather Resistant	Yes	
Indoor/Outdoor	Outdoor	Wattage	1875 W	
Mounting Type	Вох	Voltage	125.0 V	