



Hospital-Grade Tamper-Resistant 20A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade GFCI self-test One-piece, brass, triple-wipe power contacts for lasting retention.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, GFCI, Indoor, Self-Test, Tamper-Resistant
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL
Type	Outlet		

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
------------------	-----	------------------	-------

Trip Range	5±1 mA	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		
