



Spec-Grade Isolated Ground Tamper-Resistant 20A Self-Test Duplex GFCI

## Features & Benefits

Spec-Grade GFCI self-test                      One-piece, brass, triple-wipe power contacts for lasting retention.

## Specifications

### General Info

|                       |                         |                   |   |
|-----------------------|-------------------------|-------------------|---|
| Product Line          | Pass & Seymour          | Color             | Orange  |
| Finish                | Matte                   | Country Of Origin | China   |
| Number of Receptacles | 2                       | Outlet Type       | Commercial, GFCI, Indoor, Self-Test, Tamper-Resistant |
| Application Sector    | Residential/Commercial  | Standard          | cULus, UL Listed, FSUL                                |
| Warranty Type         | 1-Year Limited Warranty | Type              | Outlet  |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.73 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in  |                  |         |

### Listing Agencies / 3rd Party Agencies

cULus Listed                      Yes

### Additional Information

Product Environmental Profile                      Yes

### Technical Information

Interrupt Rating                      4 A                      Frequency Rating                      60 Hz

---

|                 |             |                |        |
|-----------------|-------------|----------------|--------|
| Trip Range      | 5±1 mA      | Amperage       | 20 A   |
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
| Voltage         | 125.0 V     |                |        |

---