

GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances and in commercial settings, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

Features & Benefits

Alarm rated at 60 db at 10 feet

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced

Feed-thru wiring configuration allows GFCI to protect downstream receptacles

Mounting screws are shipped captive in the device and wall plate for easier installation

Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box

One-piece, brass, triple-wipe power contacts for lasting retention

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly

Dual-direction test and reset button colors match the device face

Specifications

General Info

Product Line	Pass & Seymour	Color	lvory
Country Of Origin	China	Number of Receptacles	2
Features	Audible Alarm	Outlet Type	Commercial, GFCI, Indoor, Self- Test, Tamper-Resistant
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Туре	Outlet

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party	Agencies		
cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Connection	Back and side wire
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		