



Pass and Seymour  
20A 125V Heavy Duty Hospital-Grade Decorator Duplex Receptacle, Back and Side Wire, White  
Part No. 26362HGW

Heavy-Duty Decorator Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V



## Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. Heavy-duty compact design for easier installation and long lasting performance.
  - Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face.
  - Terminal compartments isolated from each other for positive conductor containment. All devices fit standard #26 opening wall plate.
  - Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.
- Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                       |                         |                   |                    |
|-----------------------|-------------------------|-------------------|--------------------|
| Product Line          | Pass & Seymour          | Color             | White              |
| Finish                | Matte                   | Country Of Origin | Mexico             |
| Number of Receptacles | 2                       | Outlet Type       | Commercial, Indoor |
| Application Sector    | Commercial              | Standard          | UL498, cUL CSA     |
| Warranty Type         | 1-Year Limited Warranty | Type              | Outlet             |

### Dimensions

---

|                  |          |                  |          |
|------------------|----------|------------------|----------|
| Product Width US | 1.322 in | Product Depth US | 0.833 in |
|------------------|----------|------------------|----------|

---

|                   |          |
|-------------------|----------|
| Product Height US | 2.635 in |
|-------------------|----------|

---

### Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

### Technical Information

---

|                     |                          |                    |              |
|---------------------|--------------------------|--------------------|--------------|
| Dielectric Strength | Withstands 2000V minimum | Temperature Rating | -40° - 60° C |
|---------------------|--------------------------|--------------------|--------------|

---

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

---

|           |             |                |        |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|

---

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|

---