



Pass and Seymour
Watertight NEMA 4X/6P Locking Plug, 20A 125V, Yellow
Part No. 26W47



Locking Watertight Plug, 20amp 125volt, NEMA Configuration L5-20, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P and IP67 rated.

Features & Benefits

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed

Dimensions

Product Height US	1.85 in	Product Length US	2.62 in
-------------------	---------	-------------------	---------

Technical Information

Phase	Single	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,
66, 67 (Plug & Connector only) Flammability
UL94V0 (boxes & wiring device interiors) Operating
Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed material s
are UV stabilized
